

RETIGA-2000R *FAST1394*

High-Sensitivity IEEE 1394 FireWire® Digital CCD Camera – Monochrome or Color

The **QImaging® Retiga-2000R** digital camera features enhanced visible-range quantum efficiency resulting in high sensitivity that is ideal for brightfield, machine vision, metrology, and metallurgical imaging applications. A progressive-scan interline CCD sensor gives a resolution of 1.92 million pixels in a 12-bit digital output. High-speed, low-noise electronics provide linear digital data for rapid image capture. The IEEE 1394 FireWire® digital interface allows ease of use and installation with a single wire. No framegrabber or external power supply is required. The Retiga 2000R includes QCapture software (Windows® and Mac OS) for real-time image preview and capture. A **Software Development Kit (SDK)** is available upon request for interfacing with custom software.

camera models

Includes: IEEE 1394 FireWire cable, IEEE 1394 PCI card, power supply, QCapture Suite software, QCapture Pro software, and access to SDK

■ **Monochrome Retiga 2000R:**

Model: RET-2000R-F-M-12-C

■ **Color Retiga 2000R:**

Model: RET-2000R-F-CLR-12-C

camera options

- RGB Color Filter for monochrome cameras (F-mount interface required), refer to data sheet for more details



- Extended Warranty



Note: Lens shown for illustration only and is not included.

features	benefits
High-Resolution, 1.92-Million-Pixel Sensor	<ul style="list-style-type: none"> ■ Highly detailed, sharp images
Large Pixels (7.4µm x 7.4µm)	<ul style="list-style-type: none"> ■ High sensitivity, high dynamic range, large well capacity
High-Speed Readout	<ul style="list-style-type: none"> ■ Previewing & focusing in real time ■ 190fps maximum frame rate ■ 10fps full resolution @ 12 bits ■ Ideal for automated imaging applications
Low-Noise Electronics	<ul style="list-style-type: none"> ■ Quantitation & imaging of low light levels
12-Bit Digitization/ 36-Bit Color Digitization (with Optional RGB Filter)	<ul style="list-style-type: none"> ■ 4096 grey levels for precise light-intensity discrimination ■ 4096 levels per channel for superior color images
External Sync & Trigger	<ul style="list-style-type: none"> ■ Tight synchronization with flashlamps, automated filters, shutters, & microscope stages
Peltier Cooling	<ul style="list-style-type: none"> ■ Minimizes thermal noise during low-light, long-exposure imaging
Binning	<ul style="list-style-type: none"> ■ Increases sensitivity for quantitation & imaging of very low light levels ■ Increases frame rate
IEEE 1394 FireWire Connection	<ul style="list-style-type: none"> ■ Simple connectivity ■ Ease of use & installation ■ Portability with laptop computer ■ Simultaneous use of multiple cameras through a single port ■ Single-cable operation (no external power supply or control unit)
Extensive Application Software Support	<ul style="list-style-type: none"> ■ Choose from a large selection of life science & industrial software for microscopy, machine vision, & video-streaming functions



adept electronic solutions
 The Machine Vision and Imaging Specialists
 Perth: +61 (08) 9242 5411
 Sydney: +61 (02) 9979 2599
 Melbourne: +61 (03) 9555 5621
 Email: adept@adept.net.au
 Web: http://www.adept.net.au

a.e.s

RETIGA-2000R FAST1394 Specifications

ccd sensor	
Light-Sensitive Pixels	1.92 million; 1600 x 1200
Binning Modes	2x2, 4x4, 8x8
ROI (Region of Interest)	From 1x1 pixels up to full resolution, continuously variable in single-pixel increments
Exposure/Integration Control	10 μ s to 17.9min in 1 μ s increments
Sensor Type	Kodak [®] KAI-2020 progressive-scan interline CCD (monochrome or color)
Pixel Size	7.4 μ m x 7.4 μ m
Linear Full Well	40,000e- (1x1); 80,000e- (2x2)
Read Noise	16e-
Dark Current	0.5e-/pix/s (non-cooled)
Cooling	Peltier thermoelectric cooling to 25°C below ambient
Digital Output	12 bits
Readout Frequency	20, 10, 5MHz
Frame Rate	10fps full resolution @ 12 bits (190fps maximum with binning and ROI functions)
camera	
Computer Platforms/ Operating Systems	Windows [®] & Mac OS*
Digital Interface	IEEE 1394 FireWire
Sustained Image Data Rate	40MB/s
Shutter Control	Electronic shutter, no moving parts
External Trigger	TTL Input
Trigger Types	Internal, Software, External
External Sync	TTL Output
Gain Control	0.451 to 21.5x
Offset Control	-2048 to 2047
Optical Interface	1", C-mount optical format
Threadmount	1/4" — 20 mount
Power Requirements	17W
Weight	845g
Warranty	2 years
Operating Environment	0 to 50°C (32 to 122°F)
Storage Temperature	-10 to 60°C
Humidity	Less than 80% non-condensing at 35°C (95 °F)



*Refer to QImaging website for detailed listing of supported operating systems.
Note: Specifications are nominal and subject to change.

FireWire and Mac OS are trademarks of Apple Computer, Inc., registered in the U.S. and other countries.
Kodak is a registered trademark of Eastman Kodak Company. Windows is a registered trademark of Microsoft Corporation in the United States and other countries. Other brand and product names are the trademarks or registered trademarks of their respective owners and manufacturers.

applications

- Brightfield, Phase-Contrast, & Darkfield Microscopy
- Live-Cell Imaging
- Pathology, Histology, & Cytology
- FISH
- Ca⁺⁺ Ratio Analysis
- Motility & Motion Analysis
- DNA Analysis
- Metallurgical Microscopy
- Semiconductor Inspection
- Manufacturing Quality Control
- Failure Analysis
- Forensic Analysis

spectral response



Tel 604.708.5061 ■ Fax 604.539.1825 ■ info@qimaging.com
www.qimaging.com

04-0017A-F